


Induction Rice Cooker

DIHR3F2




Specification

Electricity	DIHR3F2	220V, 60Hz, 1PH	Power Consumption	DIHR3F2	10500 W			
	DIHR3F2-A	340~420V, 50/60Hz, 3PH+N		DIHR3F2-A				
	DIHR3F2-E			DIHR3F2-E				
	DIHR3F2-CE1			DIHR3F2-CE1				
DIHR3F2-J	200V, 50/60Hz, 1PH	DIHR3F2-J	9000 W					
Power Connection		Direct Conection to Circuit Breaker	Max Current		15 A			
Output to Calory		9504 Kcal/h						
Dimension / Weight		730 X 660 X 1200 (mm) / 110kg						
Controller Type		Capactive button						
Per Serving		50 servings (total : 150 servings)	Memorizable Recipes		9 Recipes			
Steps per Recipe		4 steps	Container		Ø450 X 165mm (26L)			
General Output								
Warming		H1 ~ H7 (7 Steps)	Heating			1 ~ 10 (10 steps)		
Output per Warming Steps		H1	H2	H3	H4	H5	H6	H7
		40Wh	60Wh	100Wh	130Wh	170Wh	240Wh	350Wh
Functions & Features		<input checked="" type="checkbox"/> Error Code - No vessel : Error "00" - Over current indication : Error "E1" - Over voltage indication : Error "E2" (Above 265V) - Low voltage : Error "E3" (Below 180V) - Product over heated indication : Error "E4" (IGBT heat sink above 85°C) - Unstable power indication: Error "E7" - Defective PCB indication : Error "E8" - Defective Working Coil indication : Error "E9"						
		<input checked="" type="checkbox"/> One-touch Cooking System - 9 recipes can be saved at most (although the product shuts off) - You can set 4 cooking steps per recipe (each heating power and time per step) - If you set up recipe wrong, you can revise only wrong part of recipe						
		<input checked="" type="checkbox"/> Timer Setting - Between 0sec - 120min (2hr) - each steps can set-up 30min(Maximum)						
		Warranty		1 year (to be charged in case of user's negligence)				

Installation Guide

Electric Wiring



- ▶ Electricity : 380V 3PH+N
- ▶ Circuit breaker : 20A or above
- ▶ Cables : 600V, 6SQMM or above, 4 phase
- ▶ Ground cable separated : 600/1000V, 4SQMM or above

Seoul Office: #75, Achasan-ro 78-gil, Gwangjin-gu, Seoul, Republic of Korea 04969 / Tel : +82 2-444-5895 / Fax : +82 70-4694-5412

R&D Center: #209, Goraesan-ro, Wabu-eup, Namyangju-si, Gyeonggi-do, Republic of Korea 12202 / Tel : +82 2-444-5895 / Fax : +82 70-4694-5412

DIPO INDUCTION CO., Ltd. / www.dipoele.com

COPYRIGHT©2010 DIPO INDUCTION CO., LTD ALL RIGHTS RESERVED.